


Excenter waste pump **EAP**



Operating principle

The excenter waste pump is the ideal system to collect all peeled and process waste, so that it can be centralised and pumped to a central collecting area.

The Sormac excenter waste pump has the option of being combined with a collecting hopper and filling control switch. The pump is direct drive by a motor gearbox. Peeled process waste is directed into the fishtail shaped hopper or combined from additional process areas. This waste should be screened to less than 30 mm (1,18") otherwise it is necessary to provide a macerator.

The standard Sormac excenter pumps are specified for an outlet pump distance of 20 metres (66 ft) and a discharge height of 5 metres (16,4 ft). Alternative pumps are available depending on waste discharge volume.

Capacity

The capacity is max. 5 m³/hr. Bigger pumps can be delivered on request. The capacity has to fit to the expected waste flow. The quantity water should be taken into consideration which is eventually required with peeling.

Scope of supply

- excenter pump
- motor with reductor and coupling
- dry-running protection (NTC-sensor)
- adjustable legs

Options

- shredder for making smaller pieces bigger than 30 mm (1.18")
- collection hopper



Product specification

The excenter waste pump is suitable for processing peeling waste etc. of products like potatoes, carrots, celeriac. Pieces of these products can also be processed if they are smaller than 30 mm (1,18"). For larger pieces, e.g. whole potatoes, the pump must be equipped with an optional shredder.

Technical data

Type	EAP-5	EAP-17	EAP-5M	EAP-17M
Voltage	230/400 V, 50/60 Hz	230/400 V, 50/60 Hz	230/400 V, 50/60 Hz	230/400 V, 50/60 Hz
Installed power	1.5 kW	3.0 kW	4.0 kW	5.5 kW
Dimensions (LxWxH)	1,690 x 310 x 245 mm	2,430 x 380 x 335 mm	1,690 x 310 x 245 mm	2,430 x 380 x 335 mm
Capacity (max.)	± 1.2 m³/hr	± 5 m³/hr	± 1.2 m³/hr	± 5 m³/hr
Macerator	No	No	Yes	Yes

Sormac B.V.

P.O. Box 419
NL-5900 AK Venlo
Huiskensstraat 68
NL-5916 PN Venlo

T: +31 (0)77 351 84 44
F: +31 (0)77 320 48 01
info@sormac.nl
www.sormac.nl

Subject to change